



85 Railroad Drive
 Ivyland, PA 18974 USA
 Tel (215) 396-8349
 Fax (215) 396-8308
<http://www.tetratex.com>

DONALDSON MEMBRANES PRODUCT REFERENCE GUIDE

Technical Products - PTFE Thermobonded Products	PRODUCT CODE	DESCRIPTION	WIDTH
	6501	0.10 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6502	0.20 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6503	0.45 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6505	0.70 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6506	1.0 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6508	1.5 µm Expanded PTFE Membrane Bonded to Tygar 3161L Polypropylene	42"
	6521	0.10 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6522	0.20 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6523	0.45 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6525	0.70 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6526	1.0 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6528	1.5 µm Expanded PTFE Membrane Bonded to Tygar 3151 Polypropylene	42"
	6531	0.10 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6532	0.20 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6533	0.45 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6535	0.70 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6536	1.0 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6538	1.5 µm Expanded PTFE Membrane Bonded to Reemay 2275 Polyester	42"
	6552	0.20 µm Expanded PTFE Membrane Bonded to KX215 Polyethylene	46"
6561	HEPA Efficiency Pleatable PTFE Membrane Bonded to 130 g/m ² Polyester	52"	